

STYLEA

5920UOI075P41-38x38 TFR

EAN 4031582385670

Swivel castor, housing made of Polyamide, plate fitting. Wheel centre made of Polyamide, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	75 mm
Wheel width	11 mm
Castor width	54 mm
Size of Plate	38 x 38 mm
Plate hole centres	28 x 28 mm
Plate hole	4,4 mm
Swivel Interference	124 mm
Overall height	84 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.174 kg
Swivel Radius	62 mm
Hardness of tread	Shore D 75
Load capacity	50 kg
Load capacity (static)	100 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○