

STYLEA

5925UJI075S70-10X15 DOM20 TFR

EAN 4031582385731

Swivel castor with wheel brake, housing made of Polyamide, threaded stem with hexagon neck. Wheel centre made of Polyamide, Tread: TENTEprene (thermoplastic rubber). Plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	75 mm
Wheel width	8 mm
Castor width	54 mm
Threaded stem	M10 x 15 mm
Dome-Ø	20 mm
Swivel Interference	124 mm
Overall height	83 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.19 kg
Swivel Radius	62 mm
Hardness of tread	Shore D 75

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○