

# OMIKRON FLEX

9850FCP200P63 83shA HL50

EAN 4031582457407



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Tehnicki podaci

Precnik tocka.	200 mm
Sirina gazista.	50 mm
Dimenzije ploce.	140 x 110 mm
Raspored rupa na ploci.	105 x 80 mm
Rupa na ploci.	13 mm
Centralna rupa.	105 x 80 mm
Dislokacija	100 mm
Otpor okretanju.	400 mm
Sveukupna visina.	272 mm
Overall height with load	237 mm
Maximum compression	35 mm
Temperatura	-20 / +60 °C
Standard	EN_12533
Tezina	11 kg
Radius okretanja	200 mm
Tvrdoća omotaca	Shore A 83
Dinamička nosivost.	900 kg
Statika nosivost.	1200 kg

## Advantages at a glance

Otpor okretanju	● ● ● ● ○
Buka pri okretanju	● ● ● ● ○
trenje , habanje	● ● ● ● ●
zastita od korozije	● ● ● ○ ○