

## S70-8x15 / 10

EAN 4031582322033

narezan vijak sa hexagonalnim vratom



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

|                     |            |
|---------------------|------------|
| Navijeno vreteno.   | M 8 x15 mm |
| Sveukupna visina.   | 6 mm       |
| Tezina              | 0.025 kg   |
| Dinamicka nosivost. | 50 kg      |
| Staticka nosivost.  | 100 kg     |

### Advantages at a glance

|                     |           |
|---------------------|-----------|
| Otpor okretanju     | ○ ○ ○ ○ ○ |
| Buka pri okretanju  | ○ ○ ○ ○ ○ |
| trenje , habanje    | ○ ○ ○ ○ ○ |
| zastita od korozije | ● ● ● ○ ○ |