FORMA

6945UFP150B33-18,7 grey

EAN 4031582476521

BETTER MOBILITY. BETTER LIFE.

Swivel castor with wheel brake, housing made of alu die-casting, powder coated, plug-in fitting. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, precision ball bearing

Picture may differ from original product

Technical Data

Wheel diameter	150 mm
Wheel width	18 mm
Bolt-Ø	19 mm
Bolt length	25 mm
Offset	57 mm
Overall height	164 mm
Temperature	- 18 / + 120 °C
Swivel Radius	137 mm
Hardness of tread	Shore 60 A
Load capacity	135 kg

Structure & Mounting



Advantages at a glance

Roll performance	●●●●○
Movement noise	●●●●○
Attrition	●●●●○
Corrosion resistance	●●●○○

© Copyright 2024 TENTE International **www.tente.com** 12/10/2024