ALPHA

3470UFR100P62 bleu TFR

EAN 4031582485486

BETTER MOBILITY. BETTER LIFE.

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing

Picture may differ from original product

Technical Data

Wheel diameter	100 mm
Wheel width	34 mm
Size of Plate	105 x 80 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	41 mm
Swivel Interference	180 mm
Overall height	128 mm
Temperature	- 20 / + 80 °C
Standard	EN_12532
Weight	0.858 kg
Swivel Radius	91 mm
Hardness of tread	Shore A 63
Load capacity	160 kg
Load capacity (static)	320 kg

Advantages at a glance

Roll performance	●●●○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

Dimensions



Structure & Mounting



ALPHA

3470UFR100P62 bleu TFR

EAN 4031582485486

Structure & Mounting