# LINEA

## 5947UAP100P30-11 RAL9002

EAN 4031582368673

BETTER MOBILITY. BETTER LIFE.

Swivel castor with total lock, tail end of castor, housing made of Polyamide, precision ball bearing in swivel head, bolt hole. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing

Picture may differ from original product

### Technical Data

| | |
|---|---|
| Wheel diameter | 100 mm |
| Wheel width | 20 mm |
| Castor width | 82 mm |
| Centre hole | 11 mm |
| Dome-Ø | 52 mm |
| Offset | 32 mm |
| Swivel Interference | 216 mm |
| Overall height | 118 mm |
| Temperature | - 10 / + 40 °C |
| Standard | EN_12530 |
| Weight | 0.706 kg |
| Swivel Radius | 108 mm |
| Hardness of tread | Shore A 92 |
| Load capacity | 120 kg |
| Load capacity (static) | 240 kg |

### Structure & Mounting



### Advantages at a glance

| | |
|---|---|
| Roll performance | ●●●●● |
| Movement noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●●○ |

© Copyright 2024 TENTE International **www.tente.com** 12/10/2024