AGILA

2670POO4x1.25P52-95x70

EAN 4031582434972

BETTER MOBILITY. BETTER LIFE.

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, plain bearing

Picture may differ from original product

Technical Data

Wheel diameter	4 in
Wheel width	1.25 in
Plate size	3.74 x 2.76 in
Plate hole centers	1.75 x 3.00 in
Plate hole	0.43 in
Offset	1.50 in
Swivel Interference	6.93 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	5.16 in
Standard	ICWM
Swivel Radius	3.50 in
Hardness of tread	Shore D 66
Load capacity (dynamic)	330 lbs
Load capacity (static)	660 lbs

Advantages at a glance

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

© Copyright 2024 TENTE International **www.tente.com** 10/12/2024

AGILA

2670POO4x1.25P52-95x70

EAN 4031582434972

BETTER MOBILITY. BETTER LIFE.

Structure & Mounting