AGILA

267FPAP3x1.25P30-13

EAN 4031582435290

BETTER MOBILITY. BETTER LIFE.

Swivel castor with Butterfly wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: Polyurethane, precision ball bearing

Picture may differ from original product

Technical Data

Wheel diameter	3 in
Wheel width	1.25 in
Center hole	0.51 in
Offset	1.42 in
Swivel Interference	5.83 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	3.98 in
Standard	ICWM
Swivel Radius	2.92 in
Hardness of tread	Shore D 41
Load capacity (dynamic)	225 lbs
Load capacity (static)	450 lbs

Advantages at a glance

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

© Copyright 2024 TENTE International **www.tente.com** 10/12/2024

AGILA

267FPAP3x1.25P30-13

EAN 4031582435290

BETTER MOBILITY. BETTER LIFE.

Structure & Mounting