



TENTE Institutional



Excellent Design  
LEVINA



Better Mobility. Better Life.

# LEVINA Design Castor

Series 5320/Series 5370/Series 5380



TENTE LEVINA synthetic castors embody the ideal balance between ultimate design and the latest technology.


Made of high-grade synthetic material, the castor is largely resistant to all currently known detergents and disinfectants. Compliance with NSF standards permits use in the foods industry particularly in countries such as France and the USA.

## Excellent performance:


- solid housing guarantees long life
- high quality tread materials ensure exceptional rolling properties
- short brake pedal offers easy operation and smaller swivel radius
- smooth surfaces make it easy to clean
- modern castor design enhances of your product

## Available as:

5320/5370/5380	Swivel Castor
5325	Swivel Castor with wheel brake
5371/5381	Swivel Castor with directional lock
5377/5387	Swivel Castor with total lock



Electric conductive versions feature a yellow clip.



Washable versions feature a blue clip.

## Fittings:



Bolt hole



Plate



Solid stem

The bolthole allows M 10 or M 12 screws be fitted at a later date.

Mounting plate and solid stems, are available according to DIN 18867, section 8, for stainless steel castors (Castors for catering equipment).

## Colours:



RAL 9011  
graphite black



RAL 9002  
grey white

TENTE Institutional

### Series 5320

Housing and wheels are made of high grade synthetic materials, housing with blind hole for L51-10, all fittings are blue passivated



#### Wheels:

- PJO Wheel centre: Polypropylene  
Tread: TENTEprene (thermoplastic rubber) without threadguard, plain bearing
- PJP Wheel centre: Polypropylene  
Tread: TENTEprene (thermoplastic rubber) with integrated threadguards, precision ball bearing

Wheel size: 75 mm Ø  
Load capacity: 75 kg per castor according to EN 12530



### Award for excellent Design



Gute Gestaltung  
German Designer Club

nominated for the  
Federal Award  
for Product Design

### Series 5370

Housing and wheels made of high grade synthetic materials, double ball bearing swivel head, all fittings are blue passivated

#### Wheels:

- PJP Wheel centre: Polypropylene  
Tread: TENTEprene (thermoplastic rubber) with integrated threadguards, precision ball bearing
- PIP Wheel centre: Polypropylene  
Tread: Solid rubber with integrated threadguards, precision ball bearing
- UAP Wheel centre: Polyamide  
Tread: Polyurethane with integrated threadguards, precision ball bearing
- XSP electric conductive, non-marking  
Wheel centre: Polyamide  
Tread: Polyurethane with integrated threadguards, precision ball bearing

Wheel sizes:  
100 mm, 125 mm, 150 mm Ø  
Load capacity: 100 kg per castor according to EN 12530



### Series 5380



Housing and wheels made from high grade synthetic materials, double ball bearing swivel head, components stainless steel

#### Wheels:

- PJC Wheel centre: Polypropylene  
Tread: TENTEprene (thermoplastic rubber) with integrated threadguards, precision ball bearing, stainless
  - UAC Wheel centre: Polyamide  
Tread: Polyurethane with integrated threadguards, precision ball bearing, stainless
- Wheel sizes:  
100 mm, 125 mm, 150 mm Ø
- XSC electric conductive, non-marking  
Wheel centre: Polyamide  
Tread: Polyurethane with integrated threadguards, precision ball bearing, stainless

Wheel sizes: 100 mm, 125 mm Ø  
Load capacity: 100 kg per castor according to EN 12530

### LEVINA XL Series 5377/71 and 5387/81

The forwarded brake lever position guarantees excellent accessibility of the locking pedal in applications not providing an optimum fitting point for the castor lock.

Electrical conductive castors are also available.



5377/5387

5371/5381

# LEVINA Design Castors

## Options



5320 PJO 075



5325 PJO 075



5325 PJO 075 with grey pedal – optional (RAL7001)



5320 PJP 075



5325 PJP 075



5325 PJP 075 with grey pedal – optional (RAL7001)



5370 Swivel castor



5377 Swivel castor with total lock



5371 Swivel castor with directional lock



5380 Swivel castor



5387 Swivel castor with total lock



5381 Swivel castor with directional lock



5377 with grey pedal – optional (RAL7001)



5387 Swivel castor with extended fork and brake pedal, with total lock



5381 Swivel castor with extended fork and brake pedal, with directional lock

Please ask for our catalogue and visit us online: [www.tente.com](http://www.tente.com)