

# AGILA

2670PJO5x1.25P52-95x70

EAN 4031582435023

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	127 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	37 mm
Swivel Interference	176 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	159 mm
Standard	ICWM
Swivel Radius	99.5 mm
Hardness of tread	Shore A 77
Load capacity	125 kg
Load capacity (static)	250 kg

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# AGILA

2670PJO5x1.25P52-95x70

EAN 4031582435023



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

