

AGILA

2675PAP4x1.25P52-95x70

EAN 4031582435740

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	101.6 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	38 mm
Swivel Interference	236 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	131 mm
Standard	ICWM
Swivel Radius	118 mm
Hardness of tread	Shore D 41
Load capacity	125 kg
Load capacity (static)	250 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2675PAP4x1.25P52-95x70

EAN 4031582435740



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

