

FORMA

694GUF150P33 Q1-L30 grey

EAN 4031582476378

Swivel castor, central lock with three positions: directional lock, wheel lock and free movement, housing made of alu die-casting, powder coated, plate fitting. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	150 mm
Wheel width	18 mm
Castor width	80 mm
Size of Plate	92 x 64 mm
Plate hole centres	73 x 43 mm
Plate hole	9 mm
Offset	57 mm
Overall height	207 mm
Temperature	- 18 / + 120 °C
Swivel Radius	137 mm
Hardness of tread	Shore 60 A
Load capacity	135 kg

Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

FORMA

694GUFP150P33 Q1-L30 grey

EAN 4031582476378



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

