

## FOOT MASTER GATD-075-ASF-HUD

EAN 4031582495232

Swivel twin wheel castor, housing made of steel welded, zinc plated, double thrust bearing in the swivel head, grease nipple, tilting function to maintain contact with uneven floor, wheel axle with nut, plate fitting. Wheel centre made of cast iron, Tread: Polyurethane, casted, precision ball bearing.



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

### Technical Data

Wheel diameter	75 mm
Wheel width	30 mm
Castor width	131 mm
Size of Plate	112 x 112,0 mm
Plate hole centres	92 x 92 mm
Plate hole	9 mm
Dome-Ø	104 mm
Offset	30 mm
Swivel Interference	162 mm
Overall height	123 mm
Temperature	-10 / +90 °C
Weight	5.56 kg
Swivel Radius	81 mm
Load capacity	250 kg

### Dimensions



### Advantages at a glance

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○