

LINEA**5940XSP125P30-13 RAL9002**

EAN 4031582351897

Swivel castor, housing made of Polyamide, precision ball bearing in swivel head, bolt hole. Wheel centre made of Polyamide, electric conductive, tread made of Polyurethane, with threadguards, precision ball bearing

TENTE

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	125 mm
Wheel width	20 mm
Castor width	82 mm
Centre hole	13 mm
Dome-Ø	52 mm
Offset	40 mm
Swivel Interference	218 mm
Overall height	143 mm
Temperature	- 10 / + 40 °C
Standard	EN_12530
Weight	0.051 kg
Swivel Radius	109 mm
Hardness of tread	Shore A 92
Load capacity	130 kg
Load capacity (static)	260 kg

Advantages at a glance

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

Structure & Mounting