

# AGILA

267FPO03x1.25P52-95x70

EAN 4031582435269

Swivel castor with Butterfly wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	76.2 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	8 mm
Offset	36 mm
Swivel Interference	148.2 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	104 mm
Standard	ICWM
Swivel Radius	74.1 mm
Hardness of tread	Shore D 66
Load capacity	115 kg
Load capacity (static)	204 kg

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# AGILA

267FPO03x1.25P52-95x70

EAN 4031582435269



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

