

AGILA

2477PJO075B10-11x31

EAN 4031582403770

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, stem with circlip. Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

Technical Data

| | |
|-------------------------|----------------|
| Wheel diameter | 75 mm |
| Wheel width | 25 mm |
| Castor width | 43 mm |
| Metal stem with circlip | 11 x 31 mm |
| Dome-Ø | 43 mm |
| Offset | 24 mm |
| Swivel Interference | 160 mm |
| Overall height | 103 mm |
| Temperature | - 20 / + 60 °C |
| Standard | EN_12530 |
| Weight | 0.299 kg |
| Swivel Radius | 80 mm |
| Hardness of tread | Shore A 87 |
| Load capacity | 75 kg |
| Load capacity (static) | 150 kg |

Structure & Mounting



Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |