

FAN 4031582340624

Hint: TÜV Süd certified product. Washable beds must be sealed in the fitting area by the hospital bed manufacturer.



**BETTER MOBILITY. BETTER LIFE.**



Picture may differ from original product

Wheel diameter	100 mm
Wheel width	15 mm
Castor width	60 mm
Bolt-Ø	28 mm
Bolt length	96 mm
Offset	31 mm
Swivel Interference	162 mm
Overall height	129 mm
Temperature	- 30 / + 80 °C
Standard	similar_EN12531
Weight	1.39 kg
Swivel Radius	81 mm
Hardness of tread	Shore D 40
Load capacity	125 kg
Load capacity (static)	375 kg

Technical drawing of a mechanical part, likely a valve or actuator component, showing three views: a top view, a front view, and a side view.

**Top View:** Shows a circular base with a diameter of  $\phi 100$ . A central slot has a width of  $\phi 31$ . A dimension line indicates a distance of 129 from the center to the edge of the slot.

**Front View:** Shows the profile of the component. The total height is 129. The base diameter is  $\phi 100$ . A vertical dimension of 76.5 is shown from the base to the center of a hole. The hole has a diameter of  $\phi 28$ . A dimension of 96 is shown from the base to the top of the component. A dimension of 11 is shown from the base to the center of the hole. A dimension of 19 is shown from the base to the center of a hole. A dimension of 14.8 is shown from the base to the center of a hole.

**Side View:** Shows the profile of the component. The total height is 129. The base diameter is  $\phi 100$ . A vertical dimension of 76.5 is shown from the base to the center of a hole. The hole has a diameter of  $\phi 28$ . A dimension of 96 is shown from the base to the top of the component. A dimension of 11 is shown from the base to the center of the hole. A dimension of 19 is shown from the base to the center of a hole. A dimension of 14.8 is shown from the base to the center of a hole.

**Note:** S45 = Schaltwinkel 2x 45°

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# INTEGRAL TWIN

2946USX100R26-28S45 4xM8

EAN 4031582340624



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

