

AGILA

2677POO4x1.25P52-95x70

EAN 4031582435788

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head
Wheel centre made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	101.6 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	38 mm
Swivel Interference	236 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	131 mm
Standard	ICWM
Swivel Radius	118 mm
Hardness of tread	Shore D 66
Load capacity	150 kg
Load capacity (static)	300 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2677POO4x1.25P52-95x70

EAN 4031582435788



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

