

AGILA

2670PAP3x1.25P30-13

EAN 0

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	3 in
Wheel width	1.25 in
Center hole	0.51 in
Offset	1.42 in
Swivel Interference	5.83 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	3.98 in
Standard	ICWM
Swivel Radius	2.89 in
Hardness of tread	Shore D41
Load capacity (dynamic)	225 lbs
Load capacity (static)	450 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

AGILA

2670PAP3x1.25P30-13

EAN 0

Structure & Mounting



BETTER MOBILITY. BETTER LIFE.