

AGILA

2670PJP5x1.25P52-95x70

EAN 4031582435047

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	5 in
Wheel width	1.25 in
Plate size	3.74 x 2.76 in
Plate hole centers	1.75 x 3.00 in
Plate hole	0.43 in
Offset	1.46 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	6.26 in
Standard	ICWM
Swivel Radius	3.92 in
Hardness of tread	Shore A 77
Load capacity (dynamic)	275 lbs
Load capacity (static)	550 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

PRODUCT INFORMATION

AGILA

2670PJP5x1.25P52-95x70

EAN 4031582435047



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

