

AGILA

2670POO3x1.25P52-95x70

EAN 4031582

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	3 in
Wheel width	1.25 in
Plate size	3.74 x 2.76 in
Plate hole centers	1.75 x 3.00 in
Plate hole	0.31 in
Offset	1.42 in
Swivel Interference	5.83 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	4.09 in
Standard	ICWM
Swivel Radius	2.92 in
Hardness of tread	Shore D 66
Load capacity (dynamic)	255 lbs
Load capacity (static)	450 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2670POO3x1.25P52-95x70

EAN 4031582

Structure & Mounting



BETTER MOBILITY. BETTER LIFE.