

AGILA

2476DIK100R26-28S45

EAN 4031582301700

Swivel caster with central lock, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, stem with cam hole for profile bars. Wheel center made of pressed steel, Tread: solid rubber, grey non-marking, with threadguards, cone ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	3.94 in
Wheel width	1.26 in
Bolt-Ø	1.10 in
Bolt length	3.78 in
Offset	1.50 in
Swivel Interference	6.93 in
Overall height	5.43 in
Temperature	- 4 / + 185 °F
Standard	EN 12530
Weight	2.377 lbs
Swivel Radius	3.46 in
Hardness of tread	Shore A 80
Load capacity (dynamic)	175 lbs
Load capacity (static)	355 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○