

# AGILA

2675PAP3x1.25P52-95x70

EAN 4031582435559

Swivel caster with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	3 in
Wheel width	1.25 in
Plate size	3.74 x 2.76 in
Plate hole centers	1.75 x 3.00 in
Plate hole	0.43 in
Offset	1.42 in
Swivel Interference	8.82 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	4.09 in
Standard	ICWM
Swivel Radius	4.41 in
Hardness of tread	Shore D 41
Load capacity (dynamic)	225 lbs
Load capacity (static)	450 lbs

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

PRODUCT INFORMATION

# AGILA

2675PAP3x1.25P52-95x70

EAN 4031582435559



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

