

AGILA

2677PJO4x1.25P52-95x70

EAN 4031582435764

Swivel caster with total lock, trailing end of caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

| | |
|-------------------------|----------------|
| Wheel diameter | 4 in |
| Wheel width | 1.25 in |
| Plate size | 3.74 x 2.76 in |
| Plate hole centers | 1.75 x 3.00 in |
| Plate hole | 0.43 in |
| Offset | 1.50 in |
| Swivel Interference | 9.29 in |
| Axle Hole-Ø | 0.39 in |
| Hub length | 1.61 in |
| Overall height | 5.16 in |
| Standard | ICWM |
| Swivel Radius | 4.65 in |
| Hardness of tread | Shore A 77 |
| Load capacity (dynamic) | 250 lbs |
| Load capacity (static) | 500 lbs |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

AGILA

2677PJO4x1.25P52-95x70

EAN 4031582435764



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

