

AGILA

2074PJP150R26-28S45

EAN 4031582348422

Swivel Caster with central, total or directional lock, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle riveted for attaching the cover, covering of the housing made of Polypropylene, RAL 9002 grey-white, stem with cam hole for profile bars. Wheel center made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

Technical Data

Wheel diameter	5.91 in
Wheel width	1.26 in
Caster width	2.64 in
Bolt-Ø	1.10 in
Bolt length	3.78 in
Dome-Ø	2.64 in
Offset	1.77 in
Swivel Interference	9.45 in
Overall height	7.40 in
Temperature	- 4 / + 140 °F
Standard	EN 12530
Weight	2.421 lbs
Swivel Radius	4.72 in
Hardness of tread	Shore A 87
Load capacity (dynamic)	220 lbs
Load capacity (static)	440 lbs

Structure & Mounting



Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○