

# KAPPA

## 9651ITP200P63 Flat

EAN 4031582314595

Swivel caster with directional lock, housing and plate steel-welded, bright zinc plated, blue passivated, sealed swivel bearing with dual purpose bearing and tapered roller bearing, threaded king pin and locking nut secured, grease nipple, wheel axle with nut, plate fitting. Wheel center made of Aluminum, Tread: Polyurethane, casted, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


### Technical Data

Wheel diameter	7.87 in
Wheel width	1.97 in
Caster width	4.33 in
Plate size	5.31 x 4.33 in
Plate hole centers	4.13 x 3.15/2.95 in
Plate hole	0.43 in
Dome-Ø	4.37 in
Offset	2.32 in
Swivel Interference	12.60 in
Overall height	9.65 in
Temperature	+ 14 / + 140 °F
Standard	EN 12532
Weight	11.061 lbs
Swivel Radius	6.30 in
Hardness of tread	Shore A 92
Load capacity (dynamic)	1765 lbs
Load capacity (static)	3525 lbs


### Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

### Dimensions



### Structure & Mounting



# KAPPA

## 9651ITP200P63 Flat

EAN 4031582314595



BETTER MOBILITY. BETTER LIFE.

### Structure & Mounting

---

