

EAN 4031582302578

Swivel castor with central, total lock and central directional lock, frame made of pressed steel, precision ball bearing in swivel head, housing with synthetic cover, stem with cam hole for profile bars, short version. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing  
Hint: TÜV Süd certified product.



Picture may differ from original product

Wheel diameter	150 mm
Wheel width	15 mm
Castor width	75 mm
Bolt-Ø	32 mm
Bolt length	51 mm
Dome-Ø	70 mm
Offset	45 mm
Swivel Interference	248 mm
Overall height	175 mm
Temperature	- 25 / - 25 °C
Standard	EN_12531
Weight	1.421 kg
Swivel Radius	124 mm
Hardness of tread	Shore D 42
Load capacity	150 kg
Load capacity (static)	450 kg

Technical drawing of a 150mm diameter, 175mm high, 32mm diameter threaded cap. The drawing includes a top view, a side view, and a cross-sectional view. The top view shows a circular cap with a diameter of 150mm and a height of 175mm. The side view shows a cap with a diameter of 32mm and a height of 175mm. The cross-sectional view shows a cap with a diameter of 32mm and a height of 175mm. The cap has a 30-degree chamfer on the top edge and a 7mm wide base. The drawing is labeled with dimensions and a note: S30= Schatwinkel 2x 30°.

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# INTEGRAL TWIN

2944UAP150R36-32S30 4xM6

EAN 4031582302578



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

