

# AGILA

## 2477PJO075P30-11

EAN 4031582050363

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing. Castors can be mounted with standard screws of any length.



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


### Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 75 mm          |
| Wheel width            | 25 mm          |
| Castor width           | 43 mm          |
| Centre hole            | 11 mm          |
| Dome-Ø                 | 43 mm          |
| Offset                 | 24 mm          |
| Swivel Interference    | 160 mm         |
| Overall height         | 100 mm         |
| Temperature            | - 20 / + 60 °C |
| Standard               | EN_12530       |
| Weight                 | 0.267 kg       |
| Swivel Radius          | 80 mm          |
| Hardness of tread      | Shore A 87     |
| Load capacity          | 75 kg          |
| Load capacity (static) | 150 kg         |

### Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

### Dimensions



### Structure & Mounting

